



**FLOW
LEVEL
PRESSURE
ANALYTICAL
TEMPERATURE
INSTRUMENTATION
PASTEURIZATION CONTROLS**

Model RSP Sanitary Electronic Pressure Transmitter

All-welded stainless steel construction

Compact, low profile design

Meets all FDA, USDA, and CGMP requirements

3-A compliant; Third party verified in accordance with standard 74-02

Product contact surface 316L stainless steel, optional Hasteloy "C" diaphragm

Optional cap mounted LCD indicator

The Anderson RSP offers not only a low profile design, but may be ordered with built-in LCD indication. The unit meets all sanitary requirements for finish and cleanability. It is designed and manufactured to withstand the harsh process and environmental conditions encountered in the food, dairy, pharmaceutical and biotechnology industries. Its one-piece stainless steel

package design incorporates a transducer and electronic circuitry to convert pressure and/or vacuum to a proportional 4-20 mA signal. The wide variety of fittings and ranges provide flexibility in specifying the best transmitter for any application. The unit is designed to operate at high process temperatures and withstand CIP/SIP conditions. All units are supplied factory

calibrated to standard, or custom ranges. For field maintenance, non-interactive zero, and span adjustments, as well as field accessible test points are provided. The optional LCD cap mounted display can be scaled to match actual process units, 0-100% of full scale, or 4-20 mA. This useful feature provides indication directly at the process, in addition to the standard 4-20 mA output.



RSP Specifications

Accuracy (includes repeatability, linearity, and hysteresis):
 ± 0.5% of span, full scale, for standard ranges except ranges below
 0-50 psig ±1% full scale. All vacuum/pressure ranges and PSIA
 ranges are ±1%. High pressure (Homogenizer) fittings: ±.75%.

Repeatability:
 Better than 0.3% FSO

Hysteresis:
 Less than 0.2% FSO

Linearity (BFSL):
 ± 0.2% FSO

Stability:
 ± 0.3% of calibrated range/6 months

Over-Range Rating:
 2 times base range, or 12,000 psig, whichever is less

Zero and Span Adjustments:
 ± 10% of range

Output:
 4-20 mA DC

Excitation:
 12-40 VDC (Absolute), 24 VDC Nominal regulated or unregulated.
 17-45 VDC (Absolute) with display.

Loop Resistance:
 0-600 ohms at 24 VDC
 0-900 ohms at 30 VDC

Indication:
 Optional, 3-1/2 digit, .5" high LCD, cap mounted

Process Temperature Range:
 20° to 300°F (-6.7 to 148.9°C) (Horizontal mounting recommended
 for continuous operation over 275°F/135°C)

Process Temperature Effect:
 ±0.1 psig/5.5°C (10°F)

Response Time:
 200 uSec

Ambient Temp. Operating Range:
 0° to 120°F (-17.8° to 48.9°C)

Storage Temperature:
 -40° to 149°F (-40° to 65°C)

Mounting:
 Direct connection

Housing Material:
 304 Stainless Steel

Housing Ratings:
 NEMA 4X, IP-66

Wetted Parts:
 316L Stainless Steel standard;
 Hasteloy "C" diaphragm optional (Std. for homogenizer fittings)

Surface Finish (wetable parts):
 R_a max = 25 microinches (.6 microns)

Recommended Cable:
 18-24 AWG, foil shielded, and PVC coated. (3/16 - 1/4 OD insulation)

Wiring Connection:
 Screw Terminal; Accessible via removable screw cap conduit
 housing

Standards:
 Designed and manufactured to sound engineering practices in
 accordance with Article 3.3 of the PED 97/23/EC.

HOW TO ORDER



RANGE (Available Units)

025	30/0 (M)	084	0/,1000 (G)
028	30/0/15 (C)	086	0/2,000* (G)
029	30/0/30 (C)	088	0/3,000* (G)
031	30/0/60 (C)	090	0/5,000* (G)
032	30/0/100 (C)	093	0/10,000* (G)
066	0/30 (G,A)	251	-1/0/1 (B)
068	0/50 (G,A,B)	286	-1/0/2.5 (B)
069	0/60 (G)	217	-1/0/3 (B)
070	0/99 (G)	056	-1/0/4 (B)
071	0/100 (G,A)	304	-1/0/7 (B)
073	0/150 (G,A)	057	0-2 (B)
074	0/160 (G,A)	235	0-3 (B)
075	0/200 (G,A)	192	0-4 (B)
077	0/300 (G,A)	060	0-6 (B)
081	0/500 (G)	061	0-10 (B)

ENGINEERING UNITS

G	PSIG
M	Hg (inches mercury)
A	PSIA
B	BAR
C	Vacuum/Pressure ("Hg & PSIG)

FITTING

004	1-1/2" Tri-Clamp
005	2" Tri-Clamp
010	1-1/2" APC "K"
011	2" APC "K"
016	1-1/2" Cherry "I" (male)
017	2" Cherry "I" (male)
027	1-1/2" G & H "H" line (male)
028	2" G & H "H" Line (male)
044	1-1/2" #14 Bevel Seat (w/nut)
045	2" #14 Bevel Seat (w/nut)
056	High Pressure (Homogenizer) w/out Flange
057	High Pressure (Homogenizer) with 7/8" Flange
058	High Pressure (Homogenizer) with 1-1/8" Flange
059	1-1/2" NPT
117	High Pressure (Rannie)
129	38mm IDF w/Nut
131	51mm IDF w/Nut

CABLE LENGTH

00	No Cable
05	25'
10	50'
15	75'
20	100'
21	125'
22	150'
23	175'
24	200'

DIAPHRAGM FINISH

1	Standard (R _a 25)
---	------------------------------

DIAPHRAGM MATERIAL

1	316L Stainless
2	Hastelloy "C" (Standard for fittings 056, 057, 058, 117)

DISPLAY VALUE

0	None
G	PSIG**
A	PSIA
B	BAR
R	mA (milliamphere, for vac/press.)
Q	% (percent, for vac/press.)

* Available with High Pressure Fittings
 Only (056-059; 117).

** If over 2,000 PSIG, units are PSIG X 10.